

## Mighty Marker® High Purity Fine Line Marker MM-07



### Specifications



Black Ink (XV-12149)	White Paint (XV-790)	Yellow Paint (XV-791)	Red Paint (XV-830)
00107	01307	01407	01107

**Stroke**

1.2mm Fine Tip

**Replacement Nibs**

(Nylon or Polyester) #00070  
Fine Bullet Nib

**Barrel**

Aluminum

**Cap**

Indicates color of paint

**Paint Content**

4ml

**Packed Quantities**

12 per box  
144 per carton  
576 per master carton

**Temperature Range**

Use at -50°F to 150°F  
(-46°C to 66°C)

**Solvent System**

For Black: Dye Based "Alcohol"

All other colors: Pigmented Paints  
"Aromatic Solvent"


**Dry Time**

30 seconds or less

**Inks and paints meet or exceed the requirements of:**

GE# D50TF8-S7 "Nuclear Grade"  
Nuclear Plant # TEC 10000028213  
Pratt & Whitney # PWA 36700  
Rolls Royce # EMA 56752  
Chicago Bridge & Iron  
Westinghouse APP-GW-Z0-602  
Various other aerospace and nuclear grade specifications

### Directions for Use



- SHAKE WELL before use, keeping cap in place. (only necessary with paint colors)
- To start, press fiber tip down for several seconds. Repeat until tip is saturated.
- To re-ink, press down once.



**Arro-Mark®**  
COMPANY, L.L.C.

158 West Forest Avenue, Englewood NJ 07631  
Toll Free: 1-888-440-ARRO(2776)  
Phone: (201) 567-4112 | Fax: (201) 567-1373  
Website: www.arromark.com | Email: sales@arromark.com